

Z850 Zoom Stereo Microscope Series

Z850 SPECIFICATIONS

VIEWING BODY

Optical System	Twin zooming objective
Viewing Bodies	Binocular or Trinocular with 50/50 light split
ESD Protection	Viewing body is made from anti-electrostatic materials
Anti-Mold	Anti-mold and airtight design
Magnification	0.8x to 5.0x with click stops at 1x, 2x, 3x, 4x and 5x
Zoom Ratio	6.3:1
Working Distance	115mm (4.5 inches)
Viewing Angle	45 degrees
Interpupillary Distance Adjustment	52mm - 75mm
Camera Adaptability	0.4x or 0.5x c-mount adapters, photo tube
Eyepieces (with diopter adjustment)	WF10x/22mm with reticle holder (reticle size: 27mm), WF15x/16mm with reticle holder (reticle size: 20mm), WF20x/12.5mm
Auxiliary Objectives	0.5x (211mm working distance) and 2.0x (43.5mm working distance)

STANDS

Plain Focusing Stand	76mm focus mount diameter, 100mm focusing stroke, 240mm (l) x 290mm (d) x 318mm (h), 125mm black & white plate
LED Reflected/Transmitted Illuminated Stand	76mm focus mount diameter, 100mm focusing stroke, 240mm (l) x 292mm (d) x 318mm (h), 100mm clear glass and black & white plate. Variable Transmitted & Reflected LED illumination. Average LED life expectancy - 7,000 hours, Color temperature: 6200° - 7000° Kelvin
Diascopic Stand with Transmitted Illumination Attachment	76mm focus mount diameter, 100mm focusing stroke, 255mm (l) x 310mm (d) x 382mm (h), 280 mm clear glass plate. Tiltable mirror provides direct and oblique illumination. Choice of 6v20w halogen or 150w fiber optic illuminators
Pole Stand	76mm focus mount diameter, 305mm pole height, 193mm focusing stroke, 240mm (l) x 290mm (d) x 318mm (h), 125mm black & white plate
Boom Stand	Base dimensions: 254mm x 254mm (10" x 10"), Vertical Post - 365mm, Horizontal Post - 518mm. Physical weight 37 lbs.
Ball Bearing Boom Stand	Base dimensions: 254mm x 254mm (10" x 10"), Vertical Post - 394mm, Horizontal Post - 585mm. Physical weight 42 lbs.
FlexArm/Swing Arm Stand	The Swinging Arm has a 3 foot scanable range and a lockable 14.5" vertical motion range with an adjustable counterbalanced support. Horizontal or vertical clamp mount

OPTIONAL ACCESSORIES

Light Sources	LED ring & fluorescent ring lights, Fiber Optic illuminators
Digital Camera System	Micrometrics® CCD and CMOS cameras with image analysis software

OPTICAL DATA

Auxiliary Objective	Working Distance (mm)	EYEPIECE					
		WF10X/22		WF15X/16		WF20X/12.5	
		Total magnification	Visual Field (mm)	Total magnification	Visual Field (mm)	Total magnification	Visual Field (mm)
	115	8-50X	27.5-4.4	12-75X	20.0-3.2	16-100	15.6-2.5
0.5X	211	4-25X	55.0-8.8	6-37.5X	40.0-6.4	8-50X	31.2-5.0
2X	43.5	16-100X	13.8-2.2	24-150X	10.0-1.6	32-200X	7.8-1.3

UNITRON®

120-C Wilbur Place
Bohemia, NY 11716
Tel: (631) 589-6666
Fax: (631) 589-6975
Email: info@unitronusa.com
Website: www.unitronusa.com



High Performance Optics, Unsurpassed Ergonomics.

The Z850 Series is a versatile, high performance, ergonomically designed zoom stereo microscope ruggedly built to withstand years of heavy usage. With a zoom ratio of 6.3:1 the Z850 provides superior optical performance at an affordable price. Key features include:

- Binocular or trinocular viewing heads are inclined 45° and can rotate 360°.
- A best-in-class 8x to 50x magnification range with click-stops at 1x, 2x, 3x, 4x and 5x to ensure quick and consistent measurement results.
- 115mm working distance allows easy access to specimens.
- WF10x/22mm and WF15x/15mm field of view eyepieces with built-in diopter adjuster allow the image and reticle to be brought into focus at the same time. WF20x/12mm eyepieces with built-in diopter adjuster are also available, but without a reticle holder.
- Utilizing advanced design techniques the Z850's assembly is airtight preventing contamination from dust, water, oil or other particles leading to cost savings in maintenance.
- Z850 stereo bodies are made of anti-electrostatic materials allowing the microscope to discharge static electricity build-up almost instantly.
- An anti-mold design, in addition to being air tight, allows the Z850 to be used in areas of high heat and humidity without concern.



Boom Stand / Cat# 13105-Binocular

A variety of stands are available for the inspection of large size specimens. The boom stand features safety tracks on the horizontal arm and Delrin® inserts in the focus block to ensure smooth, precise movements.



Ball Bearing Boom Stand Cat# 13136-Trinocular

For users seeking precise, stable movements the ball bearing boom stand is the recommended choice. Sturdy and ruggedly built the ball bearing boom stand is ideal for observation applications where magnification adjustment and the ability to move across a sample are important considerations. The trinocular Z850 is pictured with an optional Micrometrics™ CCD camera and c- mount adapter.



Plain Focusing Stand Cat# 13130-Trinocular

The Plain Focusing Stand's thin design helps keep sample positions low resulting in increased user comfort. The focus mount is easily removable and can be positioned at two different points on the dovetail to offer maximum flexibility when working with small or large size samples. The trinocular Z850 is pictured with an optional Micrometrics™ CCD camera and c- mount adapter.



LED Illuminator Stand Cat# 13101-Binocular

Simultaneous variable reflected and transmitted LED illumination can be utilized on this stand. The compact, thin design of the base allows users to keep sample positions low and maintains easy accessibility to the variable light controls. The reflected LED illuminator is powered by a 12 volt 2 watt LED system and the transmitted LED illuminator by a 12 volt 4 watt LED system. Both light sources are variable and controlled by a universal power supply (110v – 240v).



Articulating Swing Arm Stand Cat# 13107-Binocular

Designed for maximum freedom and flexibility this stand will deliver the adjustability you need. Ideal for the inspection of specimens that require a lot of movement or to scan a large sample area, the articulating arm can be easily adjusted into hard to reach positions and moved easily out of the way.



Diascopic/Embryo Transfer Stand Cat# 13103-Binocular

This cost-effective transmitted illumination stand provides bright, even illumination across the entire magnification range. A tiltable mirror provides direct and oblique illumination for low contrast specimens. This unit can be configured with either a 6v20w halogen illuminator or 150 watt fiber optic illuminator.